



More information on the website
radwag.com/us/info,w1,W9Z

P0151 Cable

WX-013-0002



The drawings, photos and graphics used are for illustrative purposes only.

Overview

RS 232 cable for connecting a balance/scale (PUE C/31 terminal) to an Epson printer.

Standard cable length: 1,7m

Compatible with:

- Scales operated by means of PUE C31 terminal
- Scales operated by means of PUE 7.1 terminal
- PUE C31 terminal
- PUE 7.1 terminal

Compatible with (Additional Fee)

H315 HR Waterproof Platform Scale
MA X7.IC.A Moisture Analyzer
MUYA Modules
WPY Multifunctional Scale
C32 Multifunctional Scale
MA 5Y Moisture Analyzer
C315 Platform scale
WLY Scales for PGC

MA R Moisture Analyzer
AS 5Y Analytical Balance
AK-4 Automatic Mass Comparator
PS 5Y Balances for PGC
AKM-2 Automatic Mass Comparator
PS R2.H Precision Balance
WTC Precision Balance
H315 4C Platform Scale

MA X2.IC.A Moisture Analyzer
AS X7 Analytical Balance
PS X2 Precision Balance
AS X2 PLUS Analytical Balance
PS X7 Balances for PGC
WLC Precision Balance
PS R2 Precision Balance
C315.4P2 Beam Scales
WLC X7 Precision balance
PS X2 Balances for PGC
MA X2.A Moisture Analyzer
MAS Modules
MPS Modules
C315.4 Platform Scale
C32.PM Precision Balance
MA X7.A Moisture Analyzer
PS X7 Precision Balance
WPY Scales for PGC
C315.4P pallet scales
WAY 5Y.KO Manual Mass Comparator
MA 5Y.IC Moisture Analyzer

WLY Precision Balance
UMA Automatic Mass Comparator
APP 5Y.KO Manual Mass Comparator
Robotic Mass Comparators
Density measurement
WLC C/2 Precision balance
PS R1 Precision Balance
MA X2.A Moisture Analyzers
5Y.PM.KB Manual Mass Comparator
AS R2 PLUS Analytical Balance
PUE 7.1 Weighing Terminal
PS 5Y Precision Balance
Postal scales for packages
Automatic Vacuum Mass Comparators
MAS1 Modules
PMV 5Y Moisture Analyzer
XA 5Y.KO Manual Mass Comparator
PUE C315 Terminal
UYA 5Y.KO Manual Mass Comparator
AS R1 PLUS Analytical Balance
Nano-Comparator NANO.AK-4.500.5Y