
























More information on the website
radwag.com/us/info,w1,WNL

5Y.60.PM Precision balance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

| | |
|------------------------|-------|
| Maximum capacity [Max] | 60 kg |
| Minimum load | 10 g |
| Readability [d] | 0,1 g |

| | |
|----------------------------|--|
| Verification unit [e] | 1 g |
| Tare range | -60 kg |
| Minimum weight (USP) | 82 g |
| Minimum weight (U=1%,k=2) | 8,2 g |
| Repeatability (Max) | 0,15 g |
| Repeatability (5% Max) | 0,041 g |
| Linearity | ±0,3 g |
| Stabilization time | 1 s |
| Adjustment | internal (automatic) |
| OIML Class | II |
| Physical parameters | |
| Leveling system | półautomatyczny - LevelSENSING |
| Display | 10" graphic colour touchscreen |
| Weighing pan dimensions | 400×500 mm |
| Packaging dimensions | 710×610×240 mm |
| Net weight | 22 kg |
| Gross weight | 26,5 kg |
| Construction | |
| Protection class | IP 43 |
| Communication interface | 2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot |
| Power supply | Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 16V DC 1,4A max* |
| Operating temperature | +10 – +40 °C |

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration tables
Power Adapters
Additional modules
Professional Weighing Tables
Protective cover for balances
Barcode scanners

Under-pan weighing
RS 232, RS 485 cables
RS 232, RS 485 cables
Stands, wall mounting kits and mounting brackets
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter

Software

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions

