



More information on the website
radwag.com/us/info,w1,XJ0

5Y.20.PM Precision balance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	20 kg
Minimum load	-
Readability [d]	0,01 g

Verification unit [e]	-
Tare range	-20 kg
Minimum weight (USP)	8,2 g
Minimum weight (U=1%,k=2)	0,82 g
Repeatability (Max)	0,015 g
Repeatability (5% Max)	0,004 g
Linearity	±0,03 g
Stabilization time	1 s
Adjustment	internal (automatic)
OIML Class	-
Physical parameters	
Leveling system	semi-automatic - LevelSENSING
Display	10" graphic colour touchscreen
Weighing pan dimensions	200×185 mm
Packaging dimensions	520×520×280 mm
Net weight	12 kg
Gross weight	14,2 kg
Construction	
Protection class	IP 43
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 16V DC 1,4A max*
Operating temperature	+10 – +40 °C

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

MediaBox

RFID Tags

Antivibration tables

Power Adapters

Additional modules

Professional Weighing Tables

Protective cover for balances

Barcode scanners

!Balance Storage Case

Under-pan weighing

RS 232, RS 485 cables

RS 232, RS 485 cables

Stands, wall mounting kits and mounting brackets

Receipt Printer

Fingerprint Reader

RS 232 – USB Converter

Software

• E2R Weighing [WX-010-0099]

• Label Editor R02 [WX-010-0094]

• Scale Editor - EWAG 2.1 [WX-010-0173]

• E2R Weighing Records [WX-010-0038]

• RADWAG Remote Desktop [WX-010-0107]

Device dimensions

