




More information on the website  
[radwag.com/us/info,w1,XK0](http://radwag.com/us/info,w1,XK0)

# HRP 1000.5Y.KO Mass Comparator

WL-414-0027



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

F2 Calibration Range	500 – 1000 kg
M1 Calibration Range	200 – 1000 kg
M2 Calibration Range	100 – 1000 kg
Maximum capacity [Max]	1050 kg
Readability [d]	1 g
Standard repeatability [5% Max]	1,5 g
Standard repeatability [Max]	2,5 g
Permissible repeatability	5 g
Eccentricity (tested load)	1d / 1 mm
Electric compensation range	0 – +1050 kg
Stabilization time	10 s
Adjustment	internal (automatic)
<b>Physical parameters</b>	
Display	10" graphic colour touchscreen
Weighing pan dimensions	1000×800 mm

Physical parameters	
Self-centering weighing pan dimensions	600×600 (extra charge) mm
Weighing unit dimensions with self-centering weighing pan	1010×800×275 mm
Controlling device dimensions	249×170×72 mm
Comparator packaging dimensions without self-centering weighing pan	1200×1000×440 mm
Comparator packaging dimensions with self-centering weighing pan	1200×1000×485 mm
Net weight	200 kg
Net weight	200 kg
Gross weight	269 kg
Gross weight	269 kg
Recommended load speed	0,3 m/min
Maximum permissible load speed	0,6 m/min
Weighing unit dimensions without self-centering weighing pan	1010×800×182 mm
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Operating temperature	+15 – +30 °C
Operating temperature change rate	±1 °C / 12 h
Relative humidity	40% – 60%
Relative humidity change rate	±5% / 4 h

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

RFID Tags  
 Self-centering pan for HRP KO comparator  
 Additional modules  
 Protective cover for balances  
 Barcode scanners

THBR 2.0 System - Ambient Conditions Monitoring  
 RS 232, RS 485 cables  
 Receipt Printer  
 Stands, wall mounting kits and mounting brackets  
 Fingerprint Reader

## Software (Additional Fee)

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]

- RMCS Lite [WX-010-0164]

## Device dimensions



Type	A1	A2	H
HRP 200.5Y.KO	809	600	162
HRP 500.5Y.KO	809	600	162
HRP 1000.5Y.KO	1011	800	182
HRP 1500.5Y.KO	1250	1000	235
HRP 2000.5Y.KO	1250	1000	235

Dimensions in mm