



More information on the website  
[radwag.com/it/info,w1,XKT](http://radwag.com/it/info,w1,XKT)

# Bilancia multifunzione TMX15IR.6.F1.K



The drawings, photos and graphics used are for illustrative purposes only.

## Funzioni



Dosing



Labelling



Plus/Minus Control



Parts counting



Formulation



Statistics



Checkweighing

## Specifiche

### Parametri metrologici

|  |       |
|--|-------|
| Portata massima [Max]                          | 6 kg  |
| Portata minima [Min]                           | 40 g  |
| Divisione [d]                                  | 2 g   |
| Campo di tara                                  | -6 kg |
| Massima leggibilità per bilance non verificate | 0,2 g |
| Classe OIML                                    | III   |

### Parametri fisici

|                    |                                  |
|--------------------|----------------------------------|
| Display            | 15,6" graphic colour touchscreen |
| Lunghezza del cavo | 1 m                              |

| Parametri fisici              |   |
|-------------------------------|---|
| Dimensione piatto             | 300×300 mm  |
| Controlling device dimensions | 560×360×240 mm  |
| Dimensioni del pacco          | 390×570×410 mm  |
| Costruzione                   |   |
| Punteggio IP                  | IP 43 construction, IP 68 (1h max)/69 terminal  |
| Interfaccia di comunicazione  |   |
| Interfaccia                   | 4×USB 2.0 (2×USB-A, 2×M12 4P), Ethernet - 2×10/100/1000 Mbit (2×RJ45 hermetic), Profibus DP (operation mode: slave), 2×RS232, RS485 (2×M12 8P), 4IN / 4OUT (2×ports M12 8P or 2×cables fed through the cable gland) |
| Interfacce opzionali          | external buttons PRINT, TARE, START - terminal with 4IN/4OUT (M12 8P connector) is required, additional weighing platform module - max. 3 pcs, metrological parameters as in the main weighing platform             |
| Parametri elettrici           |   |
| Alimentatore                  | 100 – 240 V AC 50/60 Hz   |
| Consumo di energia            | 45 W  |
| Environmental conditions      |   |
| Ambiente di lavoro            | 0 – +40 °C  |
| Umidità relativa              | 10% – 85% RH no condensation  |



Extra payment for verification



## Accessori

Cavo seriale RS 232 (connessione bilance - Stampanti)  
 Lettore di tessere transponder  
 Cavo seriale RS 232 (connessione bilance - Stampanti ZEBRA)  
 Cavo seriale RS 232 (connessione bilance - Ethernet)  
 Display  
 Cavo seriale RS 232, RS 485  
 Lettore di codici a barre

stampanti per etichette  
 Moduli aggiuntivi della piattaforma  
 USB adapter  
 Stampanti di ricevuata  
 cavo USB (connessione bilance - stampanti)  
 RS 232 – USB Converter

## Software

- RAD Key [WX-010-0005]
- R-LAB [WX-010-0080]

- Editore di etichette R02 [WX-010-0094]