



More information on the website
radwag.com/en/info,w1,XNJ

WLC 20/A2 Precision Balance

WL-206-0022




The drawings, photos and graphics used are for illustrative purposes only.


Functions

 Plus/Minus Control

 Percent Weighing


 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 Under-pan weighing

Datasheet

Metrological parameters

| | |
|------------------------|----------|
| Maximum capacity [Max] | 20 kg |
| Minimum load | - |
| Readability [d] | 0.1 g |
| Verification unit [e] | - |
| Tare range | -20 kg |
| Repeatability | 0.1 g |
| Linearity | ±0.3 g |
| Stabilization time | 3 s |
| Adjustment | external |

| Metrological parameters | |
|-----------------------------|--|
| OIML Class | - |
| Physical parameters | |
| Leveling system | manual |
| Display | LCD (backlit) |
| Weighing pan dimensions | 195×195 mm |
| Packaging dimensions | 430×270×190 mm |
| Net weight | 2.63 kg |
| Gross weight | 3 kg |
| Construction | |
| Protection class | IP 43 |
| Communication interface | |
| Communication interface | 2×RS232, USB-A, USB-B |
| Electrical parameters | |
| Power supply | Adapter: 100 – 240V AC 50/60Hz 0.6A; 12V DC 1.2A Balance: 10 – 15VDC 0.6A max |
| Operation time on batteries | 15 h (average time) |
| Environmental conditions | |
| Operating temperature | +15 – +30 °C |
| Relative humidity | 10% – 85% RH no condensation |

Repeatability is expressed as a standard deviation from 10 weighing cycles.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.



Accessories (Additional Fee)

Balance Storage Case
 Antivibration Tables
 Power Adapters
 RS 232 cables (scale - printer)
 Cigarette lighter receptacle power supply cables
 Displays
 Under-pan weighing
 RS 232, RS 485 cables

RS 232 – Ethernet Converter
 AP2-1 Current Loop Unit
 RS 232, RS 485 cables
 RS 232 – USB Converter
 Protective cover for balances
 RS 232 cables (scale - printer)
 RS 232 – RS 485 Converter
 Receipt Printer

Software (Additional Fee)

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]

- R-Panel [WX-010-0187]
- R-Lab [WX-010-0080]

Device dimensions




WLC A2



WLC F1/K

WLC F1/R



WLC C2/K

WLC C2/R