

























More information on the website  
[radwag.com/us/info,w1,XQ4](http://radwag.com/us/info,w1,XQ4)

# XA 6/21.5Y.M Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Moveable range
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

Maximum capacity [Max]	6/21 g
Minimum load	0,1 mg
Readability [d]	1/2 µg

Verification unit [e]	1 mg
Tare range	-21 g
Standard repeatability [5% Max]	1,3 µg
Standard repeatability [Max]	3,5 µg
Standard minimum weight (USP)	2,6 mg
Standard minimum weight (U=1%, k=2)	0,26 mg
Permissible repeatability [5% Max]	2 µg
Permissible repeatability [Max]	5 µg
Linearity	±9 µg
Eccentric load deviation	15 µg
Sensitivity time drift	1×10 <sup>-6</sup> /Year×Rt
Stabilization time	~3,5 s
Adjustment	internal (automatic)
OIML Class	I
<b>Physical parameters</b>	
Leveling system	semi-automatic - LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber doors	manual
Delivery components	Microbalance, weighing pan, weighing pan shield, bottom cover, power supply, brush, fabric dust cover.
Weighing chamber dimensions	168×160×228 mm
Weighing pan dimensions	ø30 mm
Packaging dimensions	750×492×595 mm
Net weight	9,8 kg
Gross weight	14,3 kg
<b>Construction</b>	
Protection class	IP 43
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

MediaBox  
RFID Tags  
Antivibration tables  
Power Adapters  
RS 232, RS 485 cables  
Additional modules  
Anti-Draft Chamber for Microbalances  
Professional Weighing Tables  
Protective cover for balances  
Barcode scanners  
MICRO-KIT - Set of Holders for Microscale Glassware  
Label Printers

THBR 2.0 System - Ambient Conditions Monitoring  
RS 232, RS 485 cables  
Protective cover for balances  
Adapters for pipettes calibration  
Anti-Draft Chamber for XA 4Y and XA 5Y Balances  
Weighing dishes  
Antistatic ionizer  
Receipt Printer  
Fingerprint Reader  
RS 232 – USB Converter  
Under-pan weighing

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

