



More information on the website
radwag.com/us/info,w1,XQ4

XA 6/21.5Y.M Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Moveable range
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	6 / 21 g
Minimum load	0,1 mg
Readability [d]	1 / 2 µg

Verification unit [e]	1 mg
Tare range	-21 g
Standard repeatability [5% Max]	1,3 µg
Standard repeatability [Max]	3,5 µg
Standard minimum weight (USP)	2,6 mg
Standard minimum weight (U=1%, k=2)	0,26 mg
Permissible repeatability [5% Max]	2 µg
Permissible repeatability [Max]	5 µg
Linearity	±9 µg
Eccentric load deviation	15 µg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times \text{Rt}$
Stabilization time	~ 3,5 s
Adjustment	internal (automatic)
OIML Class	I

Physical parameters

Leveling system	semi-automatic – LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber doors	manual
Delivery components	Microbalance, weighing pan, weighing pan shield, bottom cover, power supply, brush, fabric dust cover.
Weighing chamber dimensions	168×160×228 mm
Weighing pan dimensions	ø30 mm
Packaging dimensions	750×492×595 mm
Net weight	9,8 kg
Gross weight	14,3 kg

Construction

Protection class	IP 43
------------------	-------

Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
-------------------------	--

Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
--------------	--

Operating temperature	+10 – +40 °C
-----------------------	--------------

Operating temperature change rate	±0,3 °C / 1 h (±1 °C / 8 h)
-----------------------------------	-----------------------------

Relative humidity	40% – 80%
-------------------	-----------

Relative humidity change rate	±1% / h (±4% / 8 h)
-------------------------------	---------------------

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration tables
Power Adapters
RS 232, RS 485 cables
Additional modules
Anti-Draft Chamber for Microbalances
Professional Weighing Tables
Protective cover for balances
Barcode scanners
MICRO-KIT - Set of Holders for Microscale Glassware
Label Printers

THBR 2.0 System - Ambient Conditions Monitoring
RS 232, RS 485 cables
Protective cover for balances
Adapters for pipettes calibration
Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Weighing dishes
Antistatic ionizer
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Under-pan weighing

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

