



More information on the website  
[radwag.com/us/info,w1,Y77](http://radwag.com/us/info,w1,Y77)

# CY10.150/300.C3.K.M3 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

## Datasheet

Maximum capacity [Max]	150 / 300 kg
Minimum load	1000 g
Readability [d]	50 / 100 g
Verification unit [e]	50 g
Tare range	-300 kg
Stabilization time	3 s
Adjustment	external
OIML Class	III

Physical parameters	
Leveling system	manual
Display	10" graphic colour touchscreen
Cable length	2,5 m
Weighing pan dimensions	500×700 mm
Packaging dimensions	850×800×270 mm
Net weight	22,7 kg
Gross weight	26,5 kg
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max; 10–19W*
Operating temperature	-10 – +40 °C
Storage temperature	-25 – +70 °C
Multiple range	YES
Features of use	
Max number of platforms	max.2

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

### MediaBox

Mild steel powder coated weighing platforms  
RFID Tags  
Power Adapters  
Additional Weighing platforms Module  
Mild steel powder coated weighing platforms  
Additional modules  
Platforms in plastic casing

### Protective cover for balances

Barcode scanners  
Label Printers  
RS 232, RS 485 cables  
Stands, wall mounting kits and mounting brackets  
Fingerprint Reader  
RS 232 – USB Converter  
Receipt Printer

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

