



More information on the website
radwag.com/us/info,w1,Y97

MPS.T.500.R1 Weighing Module

WX-016-0346



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	500 g
Preload range	50 g
Readability [d]	0,001 g
Repeatability	0,005 g
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	external
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	Stainless steel
Communication interface	RS232, max 115,2 kbps, Radwag ASCII protokół
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Balance: 12 VDC

Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%
Physical parameters	
Weighing pan dimensions	ø23 mm
Device dimensions W x D x H	220x25x75 mm
Net weight	0,5 kg



Accessories (Additional Fee)

RS 232, RS 485 cables

RS 232, RS 485 cables

Software (Additional Fee)

• R Panel [WX-010-0187]

Device dimensions W x D x H

