



More information on the website
radwag.com/en/info,w1,YMJ

RTP-RU80 Radwag Thermal Receipt Printer (RS232 + USB)



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| | |
|---------------------------------|---|
| Paper width | 80 mm |
| Print speed | max 300 mm/s |
| Roller external diameter | max 80 mm |
| Communication interface | |
| Communication interface | USB, RS232 |
| Electrical parameters | |
| Power supply | 100 – 240 V AC 50/60 Hz / 24 V DC 2.5 A |
| Environmental conditions | |
| Operating temperature | 0 – +50 °C |
| Relative humidity | 10% – 80% |
| Physical parameters | |
| Device dimensions | 127×127×129 mm |
| Net weight | 1.2 kg |

Compatible with

H315 HR Waterproof Platform Scale
MA X7.IC.A Moisture Analyzer
HX7 H Stainless steel Multifunctional Scale
HX7.4N H Multifunctional Stainless Steel Ramp Scale
HX7.4C Multifunctional Platform Scale
HX7 HR Multifunctional Scale
XA 5Y.M.A.P Microbalance for pipettes calibration
WPY Multifunctional Scale
MYA 5Y.P Microbalance for pipettes calibration
AK-5/100.STENT Automatic Balance for Stents
UMA 5Y.F Automatic Weighing System
C32 Multifunctional Scale
Stainless Steel HRP EX.H Platforms
HX5.EX-1.4P2 H Stainless Steel Beam Scales
HY10.HRP.H Stainless steel High Resolution Scale
MA 5Y Moisture Analyzer
C315 Platform scale
5Y.PM Precision Balance
MYA 5Y.F Microbalance for Filters
HX5.EX-1 HR Stainless Steel 1-Load-Cell Platform Scales
HX7.4P2 H Multifunctional Stainless Steel Beam Scales
TMX H Stainless steel Multifunctional Scale
WLY Scales for PGC
MA X2.IC.A Moisture Analyzer
AS X7 Analytical Balance
PS X2 Precision Balance
AS X2 PLUS Analytical Balance
PS X7 Balances for PGC
TMX Multifunctional Scale
C315.D Baby Scale
XA 5Y.M.A Microbalance
WLC Precision Balance
PS R2 Precision Balance
C315.4P2 Beam Scales
H315 4H Stainless Steel Platform Scale
H315 4P2.H Stainless steel Beam Scales
WLC X7 Precision Balance
HX7.4N H.LD Multifunctional Stainless Steel Ramp Scale
HX5.EX-1.4P2 C Beam Scales
CY10 Scales for PGC
PS X2 Balances for PGC
DWT/RC/HYF Checkweighers
H315 H Waterproof Platform Scale
PUE CY10 Weighing Terminal
CY10 Multifunctional Scale
HX7.4P H Multifunctional Stainless Steel Pallet Scales
MA X2.A Moisture Analyzer
HX5.EX-1.4N Stainless Steel Ramp Scales
HY10 Multifunctional Scale
PUE 5 Weighing Terminal
RS 232 cables (scale - printer)
HX5.EX-1.4 C 4-Load-Cell Platform Scales
HY10 H Stainless Steel Multifunctional Scale
H315.4 H/Z Stainless Steel Platform Scale, pit version
H315 4N.H Stainless Steel Ramp Scale
PUE 7.1.HRP High Resolution Scale
HRP EX Platforms
C315.4 Platform Scale
Susceptometer - Magnetization
HX5.EX-1.4P H Stainless Steel Pallet Scales
HY10.HRP High Resolution Scale
C32.PM Precision Balance
Automatic Balances for. Pipettes Calibration
HX7 Multifunctional Scale
HX5.EX-1.4 H/Z Stainless Steel Platform Scales, Pit Version
MA X7.A Moisture Analyzer
HX7.4 H/Z Multifunctional Stainless Steel Platform Scale, pit version
C315.O Personal Scale
WAY 5Y.KO Manual Mass Comparator
UYA 5Y Ultra-Microbalance
MA 5Y.IC Moisture Analyzer
HX5.EX-1 C 1-Load-Cell Platform Scales
MA R Moisture Analyzer
HX5.EX-1 H Waterproof Platform Scales
AS 5Y Analytical Balance
AK-4 Automatic Mass Comparator
PS 5Y Balances for PGC
AKM-2 Automatic Mass Comparator
PS R2.H Precision Balance
PUE HX5.EX Weighing Terminal
HY10.H Scales for PGC
HX5.EX-1.4 H Stainless Steel 4-Load-Cell Platform Scales
WTC Precision Balance
CY10 Precision Balance
RS 232, RS 485 cables
H315 4C Platform Scale
C315.OV Personal Scale
XA 5Y.F Analytical Balance for Filters
WLY Precision Balance
UMA Automatic Mass Comparator
H315 2K Overhead Track Scales
APP 5Y.KO Manual Mass Comparator
H315 4P.H Stainless Steel Pallet Scales
Robotic Mass Comparators
Density Measurement
WLC C/2 Precision Balance
MYA 5Y Microbalance
H315 4I.S Livestock Scales
PS R1 Precision Balance
XA 5Y Analytical Balance
MA X2.A Moisture Analyzers
5Y.PM.KB Manual Mass Comparator
USB cable (scale - printer)
AS R2 PLUS Analytical Balance
PUE C32 Weighing Terminal
PUE 7.1 Weighing Terminal
PUE HX7 Weighing Terminal
HRP 5Y.KO Mass Comparator
PS 5Y Precision Balance
Postal Scales for Packages
DWR/H Checkweighers
Automatic Vacuum Mass Comparators
PMV 5Y Moisture Analyzer
HX5.EX-1.4P C Pallet Scales
XA 5Y.KO Manual Mass Comparator
DWM HPX Checkweighers
HRP 5Y.KB Mass Comparator
H315 4I.H Stainless Steel Livestock Scales
XA 5Y.M Microbalance
RMC F Robotic Weighing System
PUE C315 Weighing Terminal
RB F Robotic Weighing System
PUE HY10 Weighing Terminal
UYA 5Y.KO Manual Mass Comparator
AS R1 PLUS Analytical Balance
UYA 5Y.F Ultra-Microbalance for Filters
Labelling Scales
DWM H2 Checkweighers
DWM/HPS Sorting Checkweigher
C315.4B Bed Scale
PUE H315 Weighing Terminal
HX7.4P Multifunctional pallet scales
Nano-Comparator NANO.AK-4.500.5Y
DWM Checkweighers
DWT/RC/HY Checkweighers
C315.K Chair Scale

H315 4N.H.LD Stainless Steel Ramp Scale
PS X7 Precision Balance
WPY Scales for PGC
XA 5Y.A Analytical Balance
HX7.4 H Multifunctional Stainless Steel Platform Scale
C315.4P pallet scales
HX7.4P2 Multifunctional Beam Scales

Roller Scales
XA 5Y.M.A.S Microbalance for stents weighing
H315 Stainless Steel Overhead Track Scales
AK-6 5Y.F Automatic Weighing System
C315.8B Ramps Bed Scale
Receipt Printer