



More information on the website
radwag.com/us/info,w1,YMJ

RADWAG RTP-RU80 Receipt Printer (RS232 + USB)



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Paper width	80 mm
Print speed	max 300 mm/s
Roller external diameter	max 80 mm
Communication interface	USB, RS232
Power supply	100 – 240 V AC 50/60 Hz / 24 V DC 2,5 A
Operating temperature	0 – +50 °C
Relative humidity	10% – 80%
Physical parameters	
Device dimensions	127×127×129 mm
Net weight	1,2 kg

Compatible with

H315 HR Waterproof Platform Scale
 MA X7.IC.A Moisture Analyzer
 HX7 H Multifunctional Scale
 HX7.4N H Multifunctional Stainless Steel Ramp Scale
 HX7.4C Multifunctional Platform Scale
 HX7 HR Multifunctional Scale
 XA 5Y.M.A.P Microbalance for pipettes calibration
 WPY Multifunctional Scale
 MYA 5Y.P Microbalance for pipettes calibration
 AK-5/100.STENT Automatic Balance for Stents
 UMA 5Y.F Automatic Weighing System
 C32 Multifunctional Scale
 Stainless steel HRP EX.H platforms
 HX5.EX-1.4P2 H Stainless steel Beam Scales
 HY10.HRP.H High Resolution Scale
 MA 5Y Moisture Analyzer
 C315 Platform scale
 5Y.PM Precision balance
 MYA 5Y.F Microbalance for Filters
 HX5.EX-1 HR Stainless Steel 1-Load-Cell Platform Scales
 HX7.4P2 H Multifunctional Stainless Steel Beam Scales
 TMX H Stainless steel Multifunctional Scale
 WLY Scales for PGC
 MA X2.IC.A Moisture Analyzer
 AS X7 Analytical Balance
 PS X2 Precision Balance
 AS X2 PLUS Analytical Balance
 PS X7 Balances for PGC
 TMX Multifunctional Scale
 C315.D Baby scale
 XA 5Y.M.A Microbalance
 WLC Precision Balance
 PS R2 Precision Balance
 C315.4P2 Beam Scales
 H315 4H Stainless Steel Platform Scale
 H315 4P2.H Stainless steel Beam Scales
 WLC X7 Precision balance
 HX7.4N H.LD Multifunctional Stainless Steel Ramp Scale
 HX5.EX-1.4P2 C Beam Scales
 CY10 Scales for PGC
 PS X2 Balances for PGC
 DWT/RC/HYF Checkweighers
 H315 H Waterproof Platform Scale
 PUE CY10 Weighing Terminal
 CY10 Multifunctional Scale
 HX7.4P H Multifunctional Stainless Steel Pallet Scales
 MA X2.A Moisture Analyzer
 HX5.EX-1.4N Stainless Steel Ramp Scales
 HY10 Multifunctional Scale
 PUE 5 Weighing Terminal
 RS 232 cables (scale - printer)
 HX5.EX-1.4 C 4-Load-Cell Platform Scales
 HY10 H Stainless Steel Multifunctional Scale
 H315.4 H/Z Stainless Steel Platform Scales, pit version
 H315 4N.H Stainless Steel Ramp Scale
 PUE 7.1.HRP High Resolution Scale
 HRP EX Platforms High Capacity
 C315.4 Platform Scale
 Susceptometer - Magnetization
 HX5.EX-1.4P H Stainless steel pallet scales
 HY10.HRP High Resolution Scale
 C32.PM Precision Balance
 Automatic Balances for. Pipettes Calibration
 HX7 Multifunctional Scale
 HX5.EX-1.4 H/Z Stainless steel platform scales, pit version
 MA X7.A Moisture Analyzer
 HX7.4 H/Z Multifunctional Stainless Steel Platform Scale, pit version
 C315.O Personal scale
 H315 4N.H.LD Stainless Steel Ramp Scale
 PS X7 Precision Balance
 WPY Scales for PGC
 WAY 5Y.KO Manual Mass Comparator
 UYA 5Y Ultra-Microbalance
 MA 5Y.IC Moisture Analyzer
 HX5.EX-1 C 1 Load Cell Platform Scales
 MA R Moisture Analyzer
 HX5.EX-1 H Waterproof Platform Scales
 AS 5Y Analytical Balance
 AK-4 Automatic Mass Comparator
 PS 5Y Balances for PGC
 AKM-2 Automatic Mass Comparator
 PS R2.H Precision Balance
 PUE HX5.EX Weighing Terminal
 HY10.H scales for PGC
 HX5.EX-1.4 H Stainless Steel 4-Load-Cell Platform Scales
 WTC Precision Balance
 CY10 Precision balance
 RS 232, RS 485 cables
 H315 4C Platform Scale
 C315.OW Personal scale
 Analytical Balance for Filters XA 5Y.F
 WLY Precision Balance
 UMA Automatic Mass Comparator
 H315 2K Overhead Track Scales
 APP 5Y.KO Manual Mass Comparator
 H315 4P.H Stainless Steel Pallet Scales
 Robotic Mass Comparators
 Density measurement
 WLC C/2 Precision balance
 MYA 5Y Microbalance
 H315 4I.S livestock scales
 PS R1 Precision Balance
 XA 5Y Analytical Balance
 MA X2.A Moisture Analyzers
 5Y.PM.KB Manual Mass Comparator
 USB cable (scale - printer)
 AS R2 PLUS Analytical Balance
 PUE C32 Weighing Terminal
 PUE 7.1 Weighing Terminal
 PUE HX7 Weighing Terminal
 HRP 5Y.KO Mass Comparator
 PS 5Y Precision Balance
 Postal scales for packages
 DWR/H Checkweighers
 Automatic Vacuum Mass Comparators
 PMV 5Y Moisture Analyzer
 HX5.EX-1.4P C Pallet scales
 XA 5Y.KO Manual Mass Comparator
 DWM HPX Checkweighers
 HRP 5Y.KB Mass Comparator
 H315 4I.H Stainless steel livestock scales
 XA 5Y.M Microbalance
 RMC F Robotic Weighing System
 PUE C315 Terminal
 RB F Robotic Weighing System
 PUE HY10 Weighing Terminal
 UYA 5Y.KO Manual Mass Comparator
 AS R1 PLUS Analytical Balance
 UYA 5Y.F Ultra-Microbalance for Filters
 Labelling Scales
 DWM H2 Checkweighers
 DWM/HPS Sorting Checkweigher
 C315.4B Bed scale
 PUE H315 Terminal
 HX7.4P Multifunctional pallet scales
 Nano-Comparator NANO.AK-4.500.5Y
 DWM Checkweighers
 DWT/RC/HY Checkweighers
 C315.K Chair scale
 Roller Scales
 XA 5Y.M.A.S Microbalance for stents weighing
 H315 Stainless steel overhead track scales

XA 5Y.A Analytical Balance
HX7.4 H Multifunctional Stainless Steel Platform Scale
C315.4P pallet scales
HX7.4P2 Multifunctional Beam Scales

AK-6 5Y.F Automatic Weighing System
C315.8B Ramps bed scale
Receipt Printer