



More information on the website  
radwag.com/us/info,w1,YMJ

# RADWAG RTP-RU80 Receipt Printer (RS232 + USB)

WX-007-0119



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Paper width	80 mm
Print speed	max 300 mm/s
Roller external diameter	max 80 mm
Communication interface	USB, RS232
Power supply	100 – 240 V AC 50/60 Hz / 24 V DC 2,5 A
Operating temperature	0 – +50 °C
Relative humidity	10% – 80%
<b>Physical parameters</b>	
Device dimensions	127×127×129 mm
Net weight	1,2 kg

## Compatible with (Additional Fee)

H315 HR Waterproof Platform Scale  
 MA X7.IC.A Moisture Analyzer  
 HX7 H Multifunctional Scale  
 HX7.4N H Multifunctional Stainless Steel Ramp Scale  
 HX7.4C Multifunctional Platform Scale  
 HX7 HR Multifunctional Scale  
 XA 5Y.M.A.P Microbalance for pipettes calibration  
 WPY Multifunctional Scale  
 MYA 5Y.P Microbalance for pipettes calibration  
 AK-5/100.STENT Automatic Balance for Stents  
 UMA 5Y.F Automatic Weighing System  
 C32 Multifunctional Scale  
 Stainless steel HRP EX.H platforms  
 HX5.EX-1.4P2 H Stainless steel Beam Scales  
 HY10.HRP.H High Resolution Scale  
 MA 5Y Moisture Analyzer  
 C315 Platform scale  
 5Y.PM Precision balance  
 MYA 5Y.F Microbalance for Filters  
 HX5.EX-1 HR Stainless Steel 1-Load-Cell Platform Scales  
 HX7.4P2 H Multifunctional Stainless Steel Beam Scales  
 TMX H Stainless steel Multifunctional Scale  
 WLY Scales for PGC  
 MA X2.IC.A Moisture Analyzer  
 AS X7 Analytical Balance  
 PS X2 Precision Balance  
 AS X2 PLUS Analytical Balance  
 PS X7 Balances for PGC  
 TMX Multifunctional Scale  
 C315.D Baby scale  
 XA 5Y.M.A Microbalance  
 WLC Precision Balance  
 PS R2 Precision Balance  
 C315.4P2 Beam Scales  
 H315 4H Stainless Steel Platform Scale  
 H315 4P2.H Stainless steel Beam Scales  
 WLC X7 Precision balance  
 HX7.4N H.LD Multifunctional Stainless Steel Ramp Scale  
 HX5.EX-1.4P2 C Beam Scales  
 CY10 Scales for PGC  
 PS X2 Balances for PGC  
 DWT/RC/HYF Checkweighers  
 H315 H Waterproof Platform Scale  
 PUE CY10 Weighing Terminal  
 CY10 Multifunctional Scale  
 HX7.4P H Multifunctional Stainless Steel Pallet Scales  
 MA X2.A Moisture Analyzer  
 HX5.EX-1.4N Stainless Steel Ramp Scales  
 HY10 Multifunctional Scale  
 PUE 5 Weighing Terminal  
 RS 232 cables (scale - printer)  
 HX5.EX-1.4 C 4-Load-Cell Platform Scales  
 HY10 H Stainless Steel Multifunctional Scale  
 H315.4 H/Z Stainless Steel Platform Scales, pit version  
 H315 4N.H Stainless Steel Ramp Scale  
 PUE 7.1.HRP High Resolution Scale  
 HRP EX Platforms High Capacity  
 C315.4 Platform Scale  
 HX5.EX-1.4P H Stainless steel pallet scales  
 HY10.HRP High Resolution Scale  
 C32.PM Precision Balance  
 Automatic Balances for. Pipettes Calibration  
 HX7 Multifunctional Scale  
 HX5.EX-1.4 H/Z Stainless steel platform scales, pit version  
 MA X7.A Moisture Analyzer  
 HX7.4 H/Z Multifunctional Stainless Steel Platform Scale, pit version  
 C315.0 Personal scale  
 H315 4N.H.LD Stainless Steel Ramp Scale  
 PS X7 Precision Balance  
 WPY Scales for PGC  
 XA 5Y.A Analytical Balance  
 UYA 5Y Ultra-Microbalance  
 MA 5Y.IC Moisture Analyzer  
 HX5.EX-1 C 1 Load Cell Platform Scales  
 MA R Moisture Analyzer  
 HX5.EX-1 H Waterproof Platform Scales  
 AS 5Y Analytical Balance  
 AK-4 Automatic Mass Comparator  
 PS 5Y Balances for PGC  
 AKM-2 Automatic Mass Comparator  
 PS R2.H Precision Balance  
 PUE HX5.EX Weighing Terminal  
 HY10.H scales for PGC  
 HX5.EX-1.4 H Stainless Steel 4-Load-Cell Platform Scales  
 WTC Precision Balance  
 CY10 Precision balance  
 RS 232, RS 485 cables  
 H315 4C Platform Scale  
 C315.OW Personal scale  
 Analytical Balance for Filters XA 5Y.F  
 WLY Precision Balance  
 UMA Automatic Mass Comparator  
 H315 2K Overhead Track Scales  
 APP 5Y.KO Manual Mass Comparator  
 H315 4P.H Stainless Steel Pallet Scales  
 Robotic Mass Comparators  
 Density measurement  
 WLC C/2 Precision balance  
 MYA 5Y Microbalance  
 H315 4I.S livestock scales  
 PS R1 Precision Balance  
 XA 5Y Analytical Balance  
 Manual susceptometers - Magnetization  
 MA X2.A Moisture Analyzers  
 5Y.PM.KB Manual Mass Comparator  
 USB cable (scale - printer)  
 AS R2 PLUS Analytical Balance  
 PUE C32 Weighing Terminal  
 PUE 7.1 Weighing Terminal  
 PUE HX7 Weighing Terminal  
 HRP 5Y.KO Mass Comparator  
 PS 5Y Precision Balance  
 Postal scales for packages  
 DWR/H Checkweighers  
 Automatic Vacuum Mass Comparators  
 PMV 5Y Moisture Analyzer  
 Automatic susceptometers - Magnetization  
 HX5.EX-1.4P C Pallet scales  
 XA 5Y.KO Manual Mass Comparator  
 DWM HPX Checkweighers  
 HRP 5Y.KB Mass Comparator  
 H315 4I.H Stainless steel livestock scales  
 XA 5Y.M Microbalance  
 RMC F Robotic Weighing System  
 PUE C315 Terminal  
 RB F Robotic Weighing System  
 PUE HY10 Weighing Terminal  
 UYA 5Y.KO Manual Mass Comparator  
 AS R1 PLUS Analytical Balance  
 UYA 5Y.F Ultra-Microbalance for Filters  
 Labelling Scales  
 DWM H2 Checkweighers  
 DWM/HPS Sorting Checkweigher  
 C315.4B Bed scale  
 PUE H315 Terminal  
 HX7.4P Multifunctional pallet scales  
 Nano-Comparator NANO.AK-4.500.5Y  
 DWM Checkweighers  
 DWT/RC/HY Checkweighers  
 C315.K Chair scale  
 Roller Scales  
 XA 5Y.M.A.S Microbalance for stents weighing

HX7.4 H Multifunctional Stainless Steel Platform Scale  
C315.4P pallet scales  
HX7.4P2 Multifunctional Beam Scales  
WAY 5Y.KO Manual Mass Comparator

H315 Stainless steel overhead track scales  
AK-6 5Y.F Automatic Weighing System  
C315.8B Ramps bed scale  
Receipt Printer