



More information on the website
radwag.com/en/info,w1,YR8

HX5.EX-1.150.H4 One Load Cell Platform Scale

WW-006-0033



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Datasheet

| Metrological parameters | |
|-------------------------|---------|
| Maximum capacity [Max] | 150 kg |
| Minimum load | 1 kg |
| Readability [d] | 50 g |
| Tare range | -150 kg |
| OIML Class | III |

| Physical parameters | |
|--------------------------|--|
| Display | 5" graphic colour |
| Cable length | 2.5 m |
| Weighing pan dimensions | 500×500 mm |
| Packaging dimensions | 610×640×550 mm |
| Net weight | 23.8 kg |
| Gross weight | 27.5 kg |
| Construction | |
| Protection class | IP 66 / 67 construction, IP 66 / 68 terminal |
| ATEX Certification | II 2G Ex ib IIB T4 Gb |
| IECEX Certification | Ex ib IIB T4 Gb |
| Construction | Stainless steel AISI304 |
| Weighing pan material | Stainless steel AISI304 |
| Communication interface | |
| Communication interface | 2×RS232, RS485 |
| Electrical parameters | |
| Power supply | 100 – 240 V AC 50/60 Hz |
| Power consumption max. | 15 W |
| Environmental conditions | |
| Operating temperature | -10 – +40 °C |
| Relative humidity | 10% – 85% RH no condensation |
| Indicator | PUE HX5.EX-1 |



Additional fee for verification



Accessories (Additional Fee)

Communication Modules
 Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX
 Weighing Terminal

Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]