




More information on the website  
[radwag.com/ja/info,w1,YXA](http://radwag.com/ja/info,w1,YXA)

# AS 120.R2 PLUS

WL-104-0191



The drawings, photos and graphics used are for illustrative purposes only.

☒☒



Autotest



Dosing



Percent Weighing



Totalizing



Parts counting



Peak hold



Newton unit measurement



Statistics



Checkweighing



Under-pan weighing



GLP Procedures



Animal weighing



Density determination

☒☒☒☒☒

☒☒☒☒☒☒	
☒☒☒☒☒☒ [Max]	120 g
☒☒☒☒	1 mg
☒☒☒☒ [d]	0,01 mg
☒☒☒☒☒☒☒☒ [e]	1 mg
☒☒☒☒	-120 g
☒☒☒☒☒☒☒☒ [5% Max]	0,012 mg

<b>Electromagnetic Compatibility</b>	
Electromagnetic Emission [Max]	0,03 mg
Electromagnetic Emission (USP)	24 mg
Electromagnetic Emission (U=1%, k=2)	2,4 mg
Electromagnetic Immunity [5% Max]	0,02 mg
Electromagnetic Immunity [Max]	0,05 mg
Temperature	±0,07 mg
Response Time	2 s
Power	Electromagnetic (Electromagnetic)
OIML Class	I
<b>Physical Characteristics</b>	
Display	Electromagnetic
Display Type	LCD (Color)
Display Size	7" (Diagonal)
Display Resolution	.....
Display Dimensions	ø90 mm + ø85 mm mm
Display Weight	545×455×575 mm
Display Height	7,04 kg
Display Width	10 kg
<b>Environmental Protection</b>	
Protection Class	IP 43
<b>Connectivity</b>	
Connectivity	2×RS232 <sup>1</sup> , 2×USB-A (Type-A), USB-B, Wi-Fi (IEEE 802.11n)
<b>Power Requirements</b>	
Power Adapter	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A : 12 – 15V DC 0,4A max
Power Consumption max.	3 W
<b>Operating Conditions</b>	
Operating Temperature	+10 – +40 °C
Operating Humidity	40% – 80%

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



## Additional Fee


USB cable (Type-A - Type-B)  
 RS 232/RS 485 cable  
 RS 232/RS 485 cable

RS 232/RS 485 cable  
 RS 232/RS 485 cable  
 RS 232/RS 485 cable


### (Additional Fee)

- [WX-010-0005]
- [WX-010-0114]
- [WX-010-0104]

- [WX-010-0187]
- [WX-010-0080]



AS R2, d = 0.01 mg



AS R2, AS R1 d = 0.1 mg