



More information on the website
radwag.com/us/info,w1,ZB0

UMA 1000.5Y Automatic Mass Comparator



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

E1	100 g ÷ 1000 g
E2	10 g ÷ 1000 g
F1	10 g ÷ 1000 g
F2	10 g ÷ 1000 g
Maximum capacity [Max]	1060 g
Readability [d]	0,005 mg
Standard repeatability [5% Max]	8 µg
Standard repeatability [Max]	12 µg
Permissible repeatability	20 µg
Eccentricity (tested load)	0 mg
Electric compensation range	-10 g ÷ +60 g
Stabilization time	30 s
Adjustment	external
Physical parameters	
Display	10" graphic colour touchscreen

Physical parameters	
Magazine positions	18
Weighing pan dimensions	ø48 mm
Weighing device dimensions	700×585×720 mm
Controlling device dimensions	460×250×195 mm
Packaging dimensions	1200×1000×1200 mm
Net weight	116 kg
Gross weight	206 kg
Supplementary weights internal	automatic
Supplementary weights external	-
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+15 ÷ +30 °C
Operating temperature change rate	±0,5°C/12h (±0,3°C/4h)
Relative humidity	40% ÷ 60%
Relative humidity change rate	±5%/12h (3%/4h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

RFID Tags
 Antivibration tables
 Additional modules
 Protective cover for balances
 Barcode scanners
 RS 232, RS 485 cables

THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 RS 232, RS 485 cables
 RS 232 cables (scale - printer)

Software

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]

- RMCS Lite [WX-010-0164]


Device dimensions



UMA-100, UMA-1000



UMA-control unit



UMA-5

