



More information on the website
radwag.com/en/info,w1,ZOC

MYA 21.5Y Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	21 g
Minimum load	0.1 mg

Metrological parameters	
Readability [d]	1 µg
Verification unit [e]	1 mg
Tare range	-21 g
Standard repeatability [5% Max]	1 µg
Standard repeatability [Max]	3 µg
Standard minimum weight (USP)	2 mg
Standard minimum weight (U=1%, k=2)	0.2 mg
Permissible repeatability [5% Max]	1.6 µg
Permissible repeatability [Max]	4 µg
Linearity	±7 µg
Eccentric load deviation	7 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	3.5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatyczny - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø90×90 mm
Weighing pan dimensions	ø26 mm
Packaging dimensions	750×492×595 mm
Net weight	9.1 kg
Gross weight	15.5 kg
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox

RFID Tags

Antivibration Tables

Power Adapters

Adapters for Pipettes Calibration

Additional modules

Anti-Draft Chamber for Microbalances

Professional Weighing Tables

Antistatic ionizer

Protective cover for balances

Barcode scanners

RS 232, RS 485 cables

THBR 2.0 System - Ambient Conditions Monitoring

RS 232, RS 485 cables

Chamber for filter weighing

Weighing dishes

Receipt Printer

Fingerprint Reader

Protective cover for balances

RS 232 – USB Converter

Software

• E2R Weighing [WX-010-0099]

• RAD Key [WX-010-0005]

• RADWAG Remote Desktop [WX-010-0107]

• Scale Editor 2.1 [WX-010-0173]

• E2R Weighing Records [WX-010-0038]

• Label Editor R02 [WX-010-0094]

• R-Lab [WX-010-0080]

• RADWAG Development Studio [WX-010-0104]

Device dimensions

