



MYA 21.5Y Microbalance






















WL-109-0010

More information on the website
radwag.com/en/info,w1,ZOC



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	21 g
Minimum load	0.1 mg

Metrological parameters	
Readability [d]	1 µg
Verification unit [e]	1 mg
Tare range	-21 g
Standard repeatability [5% Max]	1 µg
Standard repeatability [Max]	3 µg
Standard minimum weight (USP)	2 mg
Standard minimum weight (U=1%, k=2)	0.2 mg
Permissible repeatability [5% Max]	1.6 µg
Permissible repeatability [Max]	4 µg
Linearity	±7 µg
Eccentric load deviation	7 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	3.5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø 90×90 mm
Weighing pan dimensions	ø26 mm
Packaging dimensions	750×492×595 mm
Net weight	9.1 kg
Gross weight	15.5 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories (Additional Fee)

MediaBox
 RFID Tags
 Antivibration Tables
 Power Adapters
 Adapters for Pipettes Calibration
 Additional modules
 Anti-Draft Chamber for Microbalances
 Professional Weighing Tables
 Antistatic ionizer
 Protective cover for balances

Barcode scanners
 RS 232, RS 485 cables
 Chamber for filter weighing
 THBR 2.0 System - Ambient Conditions Monitoring
 RS 232, RS 485 cables
 Weighing dishes
 Receipt Printer
 Fingerprint Reader
 Protective cover for balances
 RS 232 – USB Converter

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

Device dimensions

