




# H315.4.6000.C11 Platform Scale

WP-231-0004

More information on the website  
[radwag.com/en/info,w1,ZR3](http://radwag.com/en/info,w1,ZR3)



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit measurement



Animal weighing

## Datasheet

Metrological parameters	
Maximum capacity [Max]	6000 kg
Minimum load	40 kg
Readability [d]	2 kg
Tare range	-6000 kg
Max readability for non-verified scale	500 g
OIML Class	III
Physical parameters	
Display	LCD (backlit)
Cable length	3 m

Physical parameters	
Weighing pan dimensions	2000×2000 mm
Weighing platform height	160 ± 10 mm
Packaging dimensions	2100×2100×600 mm
Scale mass with indicator	350 kg
Construction	
Protection class	IP 65 construction, IP 67 cell, IP 66 / 67 / 69 terminal
Communication interface	
Communication interface	RS232, USB
Optional interfaces	RS232 or RS485 or 4IN/4OUT or Ethernet or analog output 4-20 mA
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Optional power supply	internal rechargeable battery
Operation time on batteries	max 7h
Environmental conditions	
Operating temperature	-10 – +40 °C
Relative humidity	10% – 85% RH no condensation



Additional fee for verification



## Accessories (Additional Fee)

RS 232 cables (scale - printer)  
 Displays  
 RS 232 cables (scale - Ethernet)  
 RS 232, RS 485 cables  
 Ramps  
 Power Adapters  
 RS 232 – Ethernet Converter  
 USB adapter

Receipt Printer  
 AP2-1 Current Loop Unit  
 USB cable (scale - printer)  
 RS 232, RS 485 cables  
 Stands, wall mounting kits and mounting brackets  
 RS 232 – USB Converter  
 RS 232 cables (scale - printer)  
 RS 232 – RS 485 Converter

## Software (Additional Fee)

• RAD Key [WX-010-0005]  
 • R-Lab [WX-010-0080]

• R-Panel [WX-010-0187]  
 • Scale Editor 2.1 [WX-010-0173]