



More information on the website
radwag.com/us/info,w1,ZR5

CY10.0,6/1,5.D2.K.M3 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	0,6/1,5 kg
Minimum load	4 g
Readability [d]	0,2/0,5 g

Verification unit [e]	0,2 g
Tare range	-1,5 kg
Stabilization time	2 s
Adjustment	external
OIML Class	III
Physical parameters	
Leveling system	manualny
Display	10" graphic colour touchscreen
Weighing pan dimensions	195×195 mm
Packaging dimensions	500×310×150 mm
Net weight	3,7 kg
Gross weight	4,6 kg
Cable length	1 m
Multiple range	YES
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	12÷15V DC
Power consumption	1A
Operating temperature	-10 ÷ +40 °C
Storage temperature	-25 ÷ +70 °C
Features of use	
Max number of platforms	max.2

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
Mild steel powder coated weighing platforms
RFID Tags
Power Adapters
Additional Weighing platforms Module
Mild steel powder coated weighing platforms
Additional modules
Platforms in plastic casing

Protective cover for balances
Barcode scanners
Label Printers
RS 232, RS 485 cables
Fingerprint Reader
RS 232 – USB Converter
Receipt Printer

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

